

Serena/Daybreak Roller Shades

Light Filtering/Room Darkening

FEATURES & BENEFITS

SPECIFICATIONS

Lift Options:

Cordless Spring Motor	Acculift w/ Fabric Insert Cassette	CCO	Motorized Motorwand
convolute paper tube*	aluminum tube	1" steel tube plastic beaded chain	aluminum tube

Minimum & Maximum Widths & Lengths:

	min	max	min	max	min	max	min	max
Width	14"W	84"W	24"W	72"W	14"W	103"W	20"W	96"W
Length	12"L	84"L	24"L	72"L	12"L	120"L	18"L	120"L

Cassette Valance Dimensions:

Depth	N/A	3 $\frac{1}{2}$ " deep
Height	N/A	3" high

Minimum Depth Requirements (for mounting brackets):

	open roll/no cassette	Acculift	with cassette valance
Inside Mount	2 $\frac{1}{4}$ "	2 $\frac{5}{8}$ "	2 $\frac{5}{8}$ "
Inside Flush Mount	3"	3 $\frac{1}{2}$ "	3 $\frac{1}{2}$ "
Outside Mount	0"	0"	0"

* Note: Minimum depth for flush inside mount of standard roller shades (i.e. without a cassette valance) varies with each fabric thickness and depends on how far the shade is raised. The measurement listed is the maximum depth, fully raised, made of the thickest fabric.

Standard Factory Deductions

	open roll/no cassette	Acculift	with cassette valance
Inside Mount	1 $\frac{1}{8}$ "	1 $\frac{1}{8}$ "	1 $\frac{1}{8}$ "
Outside Mount	0"	0"	0"